

Han 24HPR VarioShell-4xM25-Set2



Image is for illustration purposes only. Please refer to product description.

Part number	10 40 124 1002
Specification	Han 24HPR VarioShell-4xM25-Set2
HARTING eCatalogue	https://harting.com/10401241002

Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR VarioShell
Type of hood/housing	Complete set
Description of hood/housing	Angled

Version

Size	24 HPR VS
VarioShell level 1	4x M25
VarioShell level 2	1x 24 B
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Details	Please note the installation manual.
Pack contents	Bulkhead mounted housing Mounting cover 1x Bulkhead mounted housing 24 HPR enlarged Fixing screws

Technical characteristics

Tightening torque	4 Nm Mounting cover 12 Nm Fixing screws 12 Nm PE screw
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP66
	IP67
	IP68
	IP69

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel

Specifications and approvals

Specifications	IEC 61984
	IEC 61373 Category 1 Class B
Approvals	CE

Commercial data

Packaging size	1
Net weight	5,106 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140175600
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466