

Features

- **High-Capacity Design** – Holds up to 18 safety padlocks, enabling simultaneous lockout operations for large teams or high-risk areas.
- **Shadow Board Visual System** – Features shadow outlines to instantly indicate missing or in-use devices, improving visibility, accountability, and operational safety.
- **Heavy-Duty Construction** – Built from 4 mm thick ACP board with a red/white high-visibility striped design for rugged, industrial use.
- **Point-of-Use Efficiency** – Ideal for installation near machinery, keeping essential lockout tools within reach to reduce response time and downtime.
- **Organised Storage** – Pre-fitted with durable nylon hooks to ensure systematic, tidy storage of padlocks and accessories.

RS PRO Shadow Lockout Station for 18 Locks - With Goods

RS Stock No.: 0642805



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Shadow Lockout Station is a complete, fully-equipped LOTO (Lockout Tagout) board designed for localised lockout operations.*
- *Ideal for high-risk work areas, this board supports the safe and organised deployment of up to 18 di-electric lockout safety padlocks, enabling rapid access to essential devices while clearly displaying their availability through shadow outlines.*
- *The shadow board format enhances operational safety by acting as a visual status indicator—making it instantly clear which devices are currently in use or missing.*
- *Can hold and manage up to 18 padlocks for simultaneous energy isolation.*
- *Comes with pre-fitted durable nylon hooks for organised and accessible storage.*
- *Ideal for Point-of-Use Lockout: Designed for use near machinery to keep lockout tools within reach.*
- *This system helps maintain compliance with safety protocols while reducing equipment downtime and improving workplace control.*

General Specifications

Type	Shadow Lockout Station
Material	4mm Aluminium Composite Panel (ACP)
Colour	Red/ White
Package	Box with corrugated fittings

Mechanical Specifications

Dimensions (W X H)	635mm X 762mm X 40mm
Width	635mm
Height	762mm
Depth	40mm
Weight	5 Kgs

Operation Environment Specifications

Withstand temperature	-20°C to +80°C
-----------------------	----------------

Accessories

Item Name	Item Description	Quantity
Lockout Padlock	Di-Electric Padlock with 42 mm Nylon Shackle - Key Different - Red	18
Hasp	Vinyl Coated Lockout Hasp - Small (25 mm)	1
Hasp	Vinyl Coated Lockout Hasp - Premier (38 mm)	1
Hasp	Di-electric Lockout Hasp - 3 Holes, 6mm Shackle	4
Cable Lockout	Squeezer Multipurpose Cable Lockout - Di-Electric - Yellow	1
Lockout Tags	Danger "Do Not Operate" Lockout Tags	20
Shadow Lockout Station	Shadow Lockout Station for 18 Locks	1