

Reciprocating Saw

JR3051T

JR3051T is a mains powered reciprocating saw with a higher continuous input rating than its predecessor and a shorter overall length.



TECHNICAL SPECIFICATIONS

Max in wood	255 mm
Max cut in pipe	130 mm
Strokes per Minute	0 – 3,000 spm
Stroke Length	30 mm
Noise sound pressure	88 dB(A)
Noise sound power	99 dB(A)
Noise K factor	3 dB(A)
Input wattage	1200 w
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Chipboard	19.5 m/sec ²
Net weight	3.2 – 3.3 kg

USER BENEFITS

- Variable speed trigger control.
- High power
- Joist hook
- Fixed shoe position
- Compact overall length 447mm
- Increased durability achieved by changing the slider holding mechanism.
- Tool-less blade change.
- Lock-on function
- Ergonomic soft grip
- Double Insulation

[Link to product - www.makita.com](http://www.makita.com)



RELATED PRODUCTS

(Recom

■ OTHER