



termékadatok

OT DALI 25/220-240/24 RGB

Termék megnevezés: OT DALI 25/220-240/24 RGB
 Termék: 4050300829463
 Mennyiség: UNPACKED (UNPACKED SELL. UNIT) (UNV) tartalmazza 1 Darab (DB)

Megtalálhatja a terméket az e-katalógusban:
http://catalog.myosram.com?~language=HU&~country=HU&it_p=4050300829463

For lamp type LED	Yes
-------------------	-----

Capabilities	
Dimming interface	DALI
Number of control inputs	1
Number of control outputs	3
Dimming range	0...100 %
Dimmable	Yes ¹⁾
Overload protection	Automatic reversible
Overtemperature protection	Automatic reversible
Short-circuit protection	Automatic reversible

Country specific categorizations	
SEG number	7980175

Certificates & standards	
Standards	acc. to DIN VDE 0875/CISPR 15/EN 55015 acc. to EN 61547 acc. to IEC 61000-3-2 acc. to IEC 61347
Type of protection	IP20

Additional product data	
Design / version	ECG standard

Logistical data	
Relative humidity	5...85 % ²⁾
Temperature range at storage	-40...85 °C

Electrical data	
Nominal wattage + Power loss	0
Nominal current	0.13 A
Rated power factor λ	0.82 ³⁾
Input voltage	198...254 V ⁴⁾
Nominal voltage	220-240 V
Mains frequency	50-60 Hz
Lamp wattage	3*8.3 W ⁵⁾
Operating frequency	1000 Hz
Output voltage	24 V ⁶⁾
Output power	24 W

Dimensions & weight	
Width	42.00 mm
Length	167.00 mm
Height	31.00 mm





Dimensions & weight	
Mounting hole spacing, length	143/148 mm
Product weight	155 g

Temperatures	
Ambient temperature range	-25...+45 °C
Operating temperature	75 °C
Max. housing temperature in case of fault	110 °C

Csomagolás fajták				
Product code	Csomagolás fajtája és tartalom	Dimensions in h x w x l	Bruttó tömeg	Mennyiség
4050300829463	UNPACKED (UNPACKED SELL. UNIT) tartalmazza 1 Darab	41,000 x 31,000 x 165,000	157,500 (0,000)	0,210
4050300829470	Karton tartalmazza 20 Darab	181,000 x 160,000 x 233,000	3.218,000 (0,000)	6,748

OTT DALI 75/220-240/24 1-4 channel

- A line voltage converter and PWM dimmer integrated in a single unit
- Integrated Touch DIM function in combination with a standard switch enables the LED modules to be dimmed with one-switch operation and the switch-on value to be saved by double-clicking Sensors enable motion-dependent lighting effects to be produced
- DALI addressable converter for 24 V LED modules
- Configurable with 1-4 output channels
- One DALI input for up to four addressable output channels
- Intelligent allocation of DALI addresses
- 75 W output can be freely distributed among up to 4x24 V PWM output channels
- Housing suitable for independent installation with strain relief

OTT DALI DIM

- Single-channel DALI compatible electronic dimmer with intelligent processor technology
- Integrated Touch DIM function in combination with a standard switch enables the LED modules to be dimmed with one-switch operation and the switch-on value to be saved by double-clicking Sensors enable motion-dependent lighting effects to be produced
- Supplied by 10 V or 24 V OPTOTRONIC units
- Non-polarity-specific control input
- Slim low-profile casing with strain relief for independent installation and luminaire integration
- Low power loss

OT 65/220-240/24 3DIM E

- Ideally suited for operation of STREETlight Advanced and STREETlight Protect modules
- Maximum output power 65 W
- Additional energy savings can be achieved dimming of connected modules via the DALI interface, control line or autonomous dimming
- The robust design of the unit protects it against moisture and mechanical stresses and ensures reliable and durable operation

Special features

- DALI control via DALI interface by DALI controllers such as DALI EASY III or DALI Professional
- Electronically reversible cutout for short-circuits, overloads and overheating
- All the units meet the necessary standards and regulations for lighting technology

- 1) 3 channel PWM output
- 2) Maximum 56 days/year at 85 %
- 3) Minimum
- 4) Permitted voltage range
- 5) Distributed among 3x 24 V PWM channels/outputs
- 6) ± 1.0 V per channel