

Technical data sheet

Article number:
151-03559

CMRCDHM8

Product Group	Heavy duty cable clamps
Product Family	screwable, Inline Ratchet Clamps
Material	Polyamide 6.6, high impact modified, heat and UV-stabilised (PA66HIRHSUV)
Colour	Black (BK)
Bundle Ø max.	50.8 mm
Bundle Ø min.	36.1 mm
CE Certification	No
Fixation Method	Screw Mount
Flammability	UL 94 HB
for Hole Ø (FH)	9.0 mm
Height (H)	30.4 mm
Length (L)	149.7 mm
Operating Temperature	-40 °C to +105 °C
Package Content	150 pcs.
Package Content packed in	pack
ROHS compliant	Yes
UV-Stabilised	Yes
Width (W)	35.1 mm

HF ✓

RoHS ✓