

FEATURES

- Suitable for indoor and outdoor
- Very strong
- Ductile and easily formed
- Recyclable
- Compatible with clamps

RS PRO Steel Round Tube, 2000mm Length, Dia. 34.2mm

RS Stock No.: 285-8996



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing a series of RS PRO general purpose steel tubes that comply fully with BS1387. These medium gauge round steel tubes are suitable for a wide range of applications at low and moderate pressure. Each tube is ready to be cut to create a frame, painted or powder coated.

RS PRO Steel Tube Options

Steel Round Tube

RS stock no: [285-8980](#) - Length 1000 mm, Dia. 34.2 mm

RS stock no: [285-9006](#) - Length 1000 mm, Dia. 42.9 mm

RS stock no: [285-9012](#) - Length 2000 mm, Dia. 42.9 mm

Galvanised Steel Round Tube

RS stock no: [285-9028](#) - Length 1000 mm, Dia. 48.8 mm

RS stock no: [285-9034](#) - Length 2000 mm, Dia. 48.8 mm

RS stock no: [285-8996](#) - Length 2000 mm, Dia. 34.2 mm

Galvanised Threaded Steel & Stainless Steel Pipe

RS stock no: [698-843](#) - Length 3.23 m, Nominal Outer Diameter 33.4 mm

RS stock no: [796-638](#) - Length 3.23 m, Nominal Outer Diameter 42.1 mm

RS stock no: [796-644](#) - Length 3.23 m, Nominal Outer Diameter 48 mm

General Specifications

Structural Element Type	Round tube
Material	Steel
Applications	Construction, Industrial equipment, Automotive manufacturing, Plumbing

Mechanical Specifications

Length	2000mm
Round Tube Outer Diameter	34.2mm
Tube Thickness	3.2mm

Approvals

Standards Met	
---------------	--

	BS 1387
--	---------

