

Angle Impact Driver LXT®

DTL061

18V • 1/4" • 60 Nm • 0 – 2 000 min⁻¹

Angle impact wrench for tight spaces

A compact and light 1/4" angle impact wrench. An angle head height of 53 mm makes this tool an ideal choice for tight spaces. A long paddle switch and handy LED light for added comfort.



Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 2000 min ⁻¹
Max Fastening Torque Impact Drill	60 Nm
Impacts per Minute (IPM)	0 - 3000 min ⁻¹
Tightening Capacity Standard Bolt	M4 - M12
Driving Shank	1/4 "
Angle length	53 mm
Sound Power Level (L _{WA})	102 dB(A)
Sound Pressure Level (L _{pA})	94 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level, Impact Tightening of Fasteners of the Maximum Capacity of the Tool	17,5 m/s ²

User benefits

- Large paddle switch trigger for easy operation
- The rubber coating on the handle ensures a firm working grip
- LED light illuminates the work site
- Ideal for working in tight spaces and overhead applications
- Quick mount for 1/4 "screwdriver
- Electric brake for maximum productivity and increased operator safety
- Variable speed control dial enables user to match the speed to the application for greater versatility
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

■ Optional AC

821550-0
Makpac case (2)



837644-1
MakPac (2) Inlay



■ Other

User manual

Parts drawing