



PLC-XD2200

- Brightness: 2200 ANSI Lumen
- Resolution: 1024 x 768 (XGA)
- Network Control and Monitoring
- Long Lamp life, up to 6000 hours
- Auto Setup
- PIN Code Security

PLC-XD2200

TECHNICAL DETAILS

Category	Business and Education
Panel	3 x 0.55" TFT Polysilicon (4:3)
Lamp	215w UHP
Brightness ANSI lumens	2200
Lamp Service Life	6,000h (Eco Mode), 4000h (Normal Mode)
Fan Noise	29dBA (Eco Mode), 34.3dBA (Normal Mode)
Standard Lens	F=2 – 2.15, f=18.38 – 22.06mm
Throw Distance Ratio	1.62 – 1.92:1
Throw Distance	1.3m – 11.8m
Contrast Ratio	500:1
Resolution in pixels	1024 x 768 (XGA)
Image size min–max (diagonal)	40" – 300"
Uniformity	85%
Bandwidth/Frequency	140MHz, Horizontal 15kHz – 100kHz, Vertical 50Hz – 100Hz
Colour Systems	NTSC, PAL, SECAM, NTSC4.43, PAL-M, PAL-N
Connections	Inputs: 1 x Dsub15 (Analog RGB, Component, S-Video) 1 x Dsub15 (Analog RGB, Monitor Out) 1 x RCA (Composite Video) 1 x Mini Jack (Audio in Computer) 2 x RCA (Audio in Video) 1 x Mini Jack (Audio Out) 1 x Dsub9 (RS232 Control) 1 x RJ45 (LAN connection)
Keystone Correction	Vertical $\pm 30^{\circ}$
HDTV Signals	1080i/50, 1080i/60, 1035i, 720p
Computer Compatibility	WUXGA, UXGA, WXGA, SXGA+, SXGA, XGA, SVGA, VGA, MAC
Zoom/Focus	1.2x / Manual
Power Consumption/Voltage	181w (Eco Mode), 218w (Normal Mode), 247w (High Mode), 0.7w (Standby Mode)
Warranty	3 Year
Dimensions (W x H x D)	333.5 x 94.2 x 247mm
Weight	2.6kg
Standard Accessories	Quick Ref Guide, Owners Manual (CD ROM), Power Cable, Remote Control
Optional Accessories	POA-CA-COMPVGA (3 RCA – Dsub15 Cable), POA-CA-VGAS (S-Video – Dsub15 Cable), POA-CA-SCART (Scart – Dsub15 Cable)

* You can use the distance calculator at www.uk.sanyo.com to determine exact image sizes and distances



Technical specifications subject to change without notice. Status 03/2010

Telephone: 01923 246363
Email: info@uk.sanyo.com
Visit: www.uk.sanyo.com

