

PSEN sI2-GL3-P switch

6N000012



Safety switch with electromagnetic guard locking, uniquely coded, for safety guard locking device PSENslock2, safe guard locking for personal protection, holding force 2000 N, 8-pin M12 male connector, single connection

Technical details

General data

Approval:	CE, UKCA, cULus Listed, FCC, IC, EAC (Eurasian), TÜV
Sensor principle:	Transponder
Coding level to ISO 14119:	High
Classification to EN 60947-5-3:	PDDb
Transponder coding:	unique coding
Suitable for series connection:	yes
unit type:	Sensor

Technical data

Electrical data

Supply voltage (V):	24 - 24 V
Type of supply voltage U1:	DC
Power consumption DC:	7.5 W

Inputs

Number of inputs:	2
DC voltage at input:	24 V DC

Semiconductor outputs

Number of OSSD outputs:	2
Number of sig. outputs:	1
S/C output short circuit proof:	Yes

Utilisation cat. to EN 60947-1:	DC-13
Environmental data	
Ambient temperature standard:	EN 60068-2-14
Ambient temperature:	-25 - 60 °C
Storage temperature standard:	EN 60068-2-1/-2
Climatic suitability standard:	EN 60068-2-78
Humidity rating:	93 % r. h. at 40 °C
Perm. operating height ASL:	2000 m
EMC to standard ...:	EN 55011: Class A, EN 60947-5-3, EN 61326-3-1
Vibration to standard ...:	EN 60068-2-6
Acc. shock to standard1:	30g
Overvoltage category:	III
Pollution degree clear.&creep.:	3
UL enclosure type:	type 1
Mechanical data	
Max. vertical offset:	5 mm
Sensor can be flush-mounted:	Yes, follow installation guide
Connection type:	M12, 8-pin male
Cable lines:	LiYY 8 x 0.25 mm ²
Product material:	Coated steel, Plastic, Stainless steel
Housing material upper part:	PBT
Height dimension:	170 mm
Width dimension:	45 mm
Depth dimension:	44 mm
Net weight:	1467 g
Gross weight:	1674 g
Transponder	
Operating frequency:	122 kHz - 128 kHz
Environment	

WEEE classification (08/2018):	5 devices (feed size < 50cm)
Commercial data	
ECLASS version:	ECLASS-13
ECLASS Reference Feature:	27272603
ETIM Version:	ETIM-9.0
ETIM Reference Group:	EG000026
ETIM Reference Feature:	EC002593
UNSPSC 25:	39122205
GTIN:	4046548092462
Volume:	0 dm3
Harmonized System Code:	85365019
Type of tariff number:	TARIC
Use of customs tariff number:	Ausfuhr, Einfuhr
Quantity per packaging unit:	1

Obligatory accessories



6N000027

PSEN sl2-L-VA actuator



6N000026

PSEN sl2-L-AL actuator

Optional accessories



540324

PSEN cable angle M12 8-pole 10m



540325

PSEN cable angle M12 8-pole 30m



540326

PSEN cable axial M12 8-pole 30m



540320

PSEN cable axial M12 8-pole 5m



540321

PSEN cable axial M12 8-pole 10m



540333

PSEN cable M12-8sf, 20m



540322

PSEN cable angle M12 8-pole 3m



540312

PSEN screw M5x20 10pcs



540323

PSEN cable angle M12 8-pole 5m



570552

PSEN sl restart interlock (padlock)



570550

PSEN sl bracket swing door



570551

PSEN sl bracket sliding door



540319

PSEN cable axial M12 8-pole 3m



6N000031

PSEN sl2 Config Key