

4561

Kevlar reinforced cut resistant glove with outstanding grip

Cut resistant glove with Zorb-It® technology which provides outstanding grip in oily conditions due to an extra absorbent sponge nitrile coating.

Features

- ▲ Cut resistant: Level D / A4
- ▲ Liner is reinforced with Kevlar for improved cut resistance
- ▲ Kevlar liner is inherently flame resistant
- ▲ Zorb-It sponge nitrile palm absorbs oil & grease to increase grip & durability in oily environments
- ▲ Manufactured using SHOWA's patented hand-former design for a comfortable fit & to minimise hand fatigue
- ▲ Seamless knitted liner prevents irritation
- ▲ Suitable for contact heat resistance up to 250°C (approx. 15 seconds)



Certifications

CAT II	EN 388:2016 + A1:2018	EN 407: 2020	ANSI 105:2016
			
	4X32C	X1XXXX	

Suitable industries & applications

Industries

- ▲ Automotive
- ▲ Construction
- ▲ Waste and Recycling

- ▲ Highways and Infrastructure
- ▲ Steel and Metals

Applications

- ▲ Component and Product Assembly
- ▲ Vehicle Assembly
- ▲ General Maintenance
- ▲ General Goods Handling

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

4561

Kevlar reinforced cut resistant glove with outstanding grip

Product information

Materials	Liner:	13 Gauge Kevlar
	Coating:	Sponge Nitrile
Colour	Yellow / Black	
Cuff Style	Elasticated Knit Wrist	

Ordering information

S	SHO45611	Items per Pack 12 x Pairs
M	SHO45612	
L	SHO45613	Items per Case 72 x Pairs
XL	SHO45614	
XXL	SHO45615	

Additional information

<p>Certification legend</p>  <p>or click here</p>	<p>Declaration of conformity</p>  <p>or click here</p>	<p>View product online</p>  <p>or click here</p>
--	---	---

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747