



Conversion Adapter IEC 320 (65°)/T13 black



Item No.: 1499592
EAN Code: 7611007521172

Description

Conversion Adapter IEC 320 (65°)/T13 black

Specifications

Type	Adapter
Brand	STEFFEN
Model	Type 13 - C14
Number of Sockets	1
Socket Type	Type 13
Increased Touch Protection	No
Product Colour	Black
Rated Current	10 A
Rated Voltage	250 V
Rated Power	2500 W
Plug Type	C14
Main Material	Plastic
Halogen-Free	No
UV Resistance	No
Application	Indoor

IP Rating	IP20
Operating Temperature Range	-20...+65 °C
Product Height	50 mm
Product Width	40 mm
Product Depth	60 mm
Net Weight	0.04 Kg
Packaging	Blister
