

Datasheet

HSS 3 Piece TiN Coated Cone Cutter

RS Stock number [221-579](#)



Description:

High Speed Steel tapered cone cutter for power tool use for drilling clean holes in plastic, PC boards, alloys and sheet metal up to 2mm thick. Comes in a metal case.

Specifications:

Kit Contents:	3 to 14, 6 to 20, 16 to 30.5 mm Step Drill Bits
Largest Head Diameter:	30.5 mm
Material:	HSS
Maximum Shank Diameter:	10 mm
Number of Pieces:	3
Smallest Head Diameter:	3 mm
Surface:	Titanium Nitride Coating