



PW3 HOLSTER WORK TROUSERS

DESCRIPTION

Rugged trouser made from Kingsmill polyester/cotton 300g fabric with a modern fit and adjustable leg length. Packed full of features to offer superb function and performance including; top loading pre-shaped knee pad pockets, triple stitched seams, crotch gusset to reduce stress and prevent seam failure and a side leg cargo pocket. Pockets have oxford reinforcement for extra durability.

COMPOSITION

-  **Titanmill Plus: 65% Polyester, 35% Cotton, 300g**
-  **100% Polyester, 600D Oxford, PU Coated, 210g**
-  **Zoom Grey/Black 28-48**

FEATURES

- Durable polycotton fabric for high performance and maximum wearer comfort
- Reinforced panels in high wear areas for maximum durability
- Reflective piping for increased visibility
- Top-loading knee pad pockets for quick and easy access
- Swing away tool pockets
- 12 Pockets for ample storage
- 2 Side pockets
- 2 back pockets with one open and one featuring a flap
- 1 Thigh pocket with zip closure
- 1 Cargo pocket
- 1 Rule pocket
- 1 Pen pocket

STANDARDS

EN 14404: 2004 + A1: 2010 Type 2 Level 0 (When used in combination with S156)

COLOUR / SIZES

| SKU     | COLOUR | SIZE RANGE |
|---------|--------|------------|
| T602ZBR | ZOOM   | 28-14      |

FEATURES



**DETACHABLE ID POCKET**  
ID card holder for ID card display



**MACHINE WASHABLE AT 60°C**  
Reusable and machine washable at 60 degrees



**UPF 40+**  
40+ UPF rated fabric to block 98% of UV rays



**PERFORMANCE WORKWEAR**  
PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

**GET THE  
COLLECTION**



TECHINCAL INFORMATION



**OEKO-TEX certification**  
13.HCN.29764

- Wash garment inside out
- Wash garment inside out and fully fastened
- Wash with similar colours
- Wash dark colours separately

| Item      | Colour Fit      | Len (cm) | Wid (cm) | Hgt (cm) | Weight (Kg) | Cubic (m³ ) | EAN13         | GTIN/DUN14     |
|-----------|-----------------|----------|----------|----------|-------------|-------------|---------------|----------------|
| T602ZBR28 | Zoom Grey/Black | 65       | 45       | 36       | .960        | 5850.000    | 5036108291519 | 15036108781680 |
| T602ZBR30 | Zoom Grey/Black | 65       | 45       | 36       | .979        | 5850.000    | 5036108290031 | 15036108780256 |
| T602ZBR32 | Zoom Grey/Black | 65       | 45       | 36       | 1.003       | 5850.000    | 5036108290048 | 15036108780263 |
| T602ZBR33 | Zoom Grey/Black | 65       | 45       | 36       | 1.080       | 5850.000    | 5036108297498 | 15036108787255 |
| T602ZBR34 | Zoom Grey/Black | 65       | 45       | 36       | 1.070       | 5850.000    | 5036108290055 | 15036108780270 |
| T602ZBR36 | Zoom Grey/Black | 65       | 45       | 36       | 1.080       | 5850.000    | 5036108290062 | 15036108780287 |
| T602ZBR38 | Zoom Grey/Black | 65       | 45       | 36       | 1.130       | 5850.000    | 5036108290079 | 15036108780294 |
| T602ZBR40 | Zoom Grey/Black | 65       | 45       | 36       | 1.120       | 5850.000    | 5036108290086 | 15036108780300 |
| T602ZBR41 | Zoom Grey/Black | 65       | 45       | 36       | 1.150       | 5850.000    | 5036108297504 | 15036108787262 |
| T602ZBR42 | Zoom Grey/Black | 65       | 45       | 36       | 1.160       | 5850.000    | 5036108290093 | 15036108780317 |
| T602ZBR44 | Zoom Grey/Black | 65       | 45       | 36       | 1.140       | 5850.000    | 5036108291526 | 15036108781697 |
| T602ZBR46 | Zoom Grey/Black | 65       | 45       | 36       | 1.180       | 5850.000    | 5036108291533 | 15036108781703 |
| T602ZBR48 | Zoom Grey/Black | 65       | 45       | 36       | 1.180       | 5850.000    | 5036108291540 | 15036108781710 |