VS-15-ST-DSUB-EG - D-SUB connector

1688874

https://www.phoenixcontact.com/gb/products/1688874

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

D-SUB contact insert, shell size 2, with 15 signal contacts, type of contact pin, with solder cup, straight, fixing with a 3 mm hole, for panel mounting frame and sleeve housing VS-15-...

Your advantages

- D-SUB 15 connection
- Easy assembly
- Compatible with IP67 sleeve housing and panel-mount frame

Commercial data

Item number	1688874
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABNCAA
Product key	ABNCAA
GTIN	4017918823023
Weight per piece (including packing)	8.59 g
Weight per piece (excluding packing)	7.43 g
Customs tariff number	85366990
Country of origin	DE

VS-15-ST-DSUB-EG - D-SUB connector

1688874

https://www.phoenixcontact.com/gb/products/1688874

Technical data

Product properties

Product type	Contact insert
Type	D-SUB
Number of positions	15
Connection profile	D-SUB 15
Shielded	no

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage in acc. with IEC 61076-2-101	400 V
Rated voltage (III/3)	125 V
Rated surge voltage	1 kV
Rated current	5 A (at 20 °C)
Test voltage	1200 V
Transmission medium	Copper

Connection data

Connection method	Solder cup

Dimensions

Width	14.4 mm
Height	39.5 mm
Length	12.9 mm

Material specifications

Flammability rating according to UL 94	V0
Housing material	Steel, tin-plated
Contact material	Copper alloy
Contact surface material	Hard gold-plated over nickel
Contact carrier material	PBT-GF

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 50
Insertion force per signal contact	≤ 3.40 N

Environmental and real-life conditions

Ambient conditions

VS-15-ST-DSUB-EG - D-SUB connector

1688874

https://www.phoenixcontact.com/gb/products/1688874

Degree of protection	IP20
Ambient temperature (operation)	-55 °C ... 125 °C

Mounting

Mounting type	Hole

VS-15-ST-DSUB-EG - D-SUB connector

1688874

https://www.phoenixcontact.com/gb/products/1688874

Drawings

Schematic diagram



VS-15-ST-DSUB-EG - D-SUB connector

1688874

https://www.phoenixcontact.com/gb/products/1688874

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/gb/products/1688874

UL Recognized
Approval ID: E118976

VS-15-ST-DSUB-EG - D-SUB connector

1688874

https://www.phoenixcontact.com/gb/products/1688874

Classifications

ECLASS

ECLASS-13.0	27440302
ECLASS-15.0	27440323

ETIM

ETIM 10.0	EC001132

UNSPSC

UNSPSC 21.0	39121400

VS-15-ST-DSUB-EG - D-SUB connector

1688874

https://www.phoenixcontact.com/gb/products/1688874

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	c30472e6-5c56-46a0-a450-62f6874c6344

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk