







RECOMMEND MINIMUM MOUNTING PITCH



PANEL CUT OUT



PCB LAYOUT
(CONNECTOR REAR VIEW)

- RJ45 CONTACTS
- RJ45 SHELL GROUND CONTACT
- CONNECTOR LOCATION PINS

RJXS8FP25VP

SERIES PREFIX
CONTACT LAYOUT (RJ45 STYLE)
GENDER
THERMOPLASTIC 3.8mm to 5.0mm WITH CAP
TRANSMISSION CLASS (CAT5e)
HORIZONTAL MOUNT (PCB THRU HOLE)
POTTED



UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE:		THIS DOCUMENT IS THE PROPERTY OF AMPHENOL AUSTRALIA PTY. LTD. NO PART THEREOF MAY BE REPRODUCED AND USED WITHOUT THE PRIOR WRITTEN CONSENT OF THE OWNER		Amphenol Australia Pty.Ltd, 22 Industry Blvd Carrum Downs, VIC 3201	
LINEAR	ANGULAR	MATERIAL:	DRN: J.W	DATE: 30/11/2023	TITLE: XLRnet,VERT,IP65, POTTED,UNSHIELDED, W/CAP, PANEL THICKNESS 3.8-5.0
X ±10 X.X ±5 X.XX ±1	X° ±1 X°X' ±30' X°XX' ±15'	SEE COMPONENTS	CKD: P.M.	DATE: 30/11/2023	PART No: RJXS8FP25VP
BREAK ALL SHARP EDGES AND REMOVE ALL BURRS	DO NOT SCALE	FINISH: SEE COMPONENTS	APP'D: P.M.	DATE: 30/11/2023	DRAWING No. 55011544-100-1
DIMENSIONS IN MILLIMETRES	THIRD ANGLE PROJECTION	SCALE: NTS	SIZE: A3		REV 1 SHEET 2/2