

# Datasheet

## LED 7W Shaver Light



### Description

This dual voltage LED shaver light is designed for use in bathrooms. The voltage can be selected to suit the appliance.

### Features

- Energy efficient replacement for old fashioned 60W striplight versions
- 230V or 115V selectable voltage output on shaver socket
- Epistar SMD LED tray provides uniform illumination
- Daylight output (6000K)
- Light is pull cord operated
- Rated life of 30,000 hours
- 2 year guarantee

### Range

LED 7W Shaver Light                      7959375

### Material

Body                      White polycarbonate  
Diffuser                      Clear polycarbonate

### Technical Specification

Input voltage	230V~ 50Hz
Output voltage	115V/230V
Lamp	Epistar SMD LED
Wattage	7W
Lumen output	480lm
Lumens per watt	68.5lm/W
CRI	Ra 70
Beam angle	120°
IP Rating	IP20

\*The shaver socket is not designed for continuous use or loads exceeding 20VA

### Standards

- EN60598-2-1:1989
- EN60598-1:2008+A11:2009
- EN55015:2006+A1:2007
- EN61547:1995+A1:2000
- EN61000-3-2:2006
- EN61000-3-3:1995+A1:2001+A2:2005
- EMC Directive (2004/108/EC)
- LVD 2006/95/EC

### Dimensions

Length	490mm
Height	58mm
Depth	70mm