

FEATURES

- High accuracy K type thermocouple material throughout
- Ideal for the temperature measurement of surfaces
- Supplied with 1.2m cable
- Terminated with moulded mini plug

RS PRO K Type Surface Temperature Probe (150 x 4mm)

RS Stock No.: 204-8397



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Temperature Probes



Product Description

This K type thermocouple sensor is manufactured with a straight handle for fine control, 1.2m durable polyurethane cable, terminated with a moulded mini thermocouple plug. The probe features a robust stationary sensing tip which is ideal for wide range applications whereby a flat surface needs to be monitored.

General Specifications

Series	RS PRO
Probe Type	Surface
Probe Tip type	Stationary disc
Sensor Type	K Type Thermocouple
Minimum Temperature Measurement	-50°C
Maximum Temperature Measurement	600°C
Response Time	3 secs (96% of value on clean metal)
Best Accuracy	±1.5°C (±0.25%)
Accuracy Class	Class I
Connector Type	Mini plug
Operating Temperature	-50 to 600°C
Storage Temperature	-20 to 80°C
Applications	Industrial, HVAC

Mechanical Specifications

Probe Diameter	4mm
Probe Length	150mm
Probe Sheath Material	316SS
Mounting Style	Handheld
Process Connection	N/A
Cable Length	1.2m
Cable Insulation Material	Polyurethane

Temperature Probes



Protection Category

IP Rating V	Water resistant
-------------	-----------------

Additional Information

EAN	5060379945499
Custom Tariff Number	90259000

Classification

eCI@ss Version	32-12-03-90
UNSPSC Version	41112219

Accessories

RS PRO Stock No.:	Accessory Description	Image		

Temperature Probes



Similar Products

Parameters	204-8394	342-8956	342-8962	342-8978	255-550
Probe Type	Surface	Surface	Surface (high temp)	Surface (extra high temp)	Surface (bow probe)
Sensor Type	K type thermocouple	K type thermocouple	K type thermocouple	K type thermocouple	K type thermocouple
Temperature Measurement Range		-200 to 300°C	-50 to 600°C	0 to 1100°C	-50 to 200°C
Response Time	3 secs (96% of value on clean metal)	0.1 secs (96% of value on clean metal)	3 secs (96% of value on clean metal)	30 secs (96% of value on clean metal)	010 secs (96% of value on clean metal)
Connector Type	Mini plug	Mini plug	Mini plug	Mini plug	Mini plug
Dimensions	200 x 6mm	110 x 10mm	110 x 6mm	210 x 12mm	110 x 60mm
Mounting Style	Handheld	Handheld	Handheld	Handheld	Handheld
Process Connection	N/A	N/A	N/A	N/A	N/A
Cable Length	1m coiled cable	2m coiled cable	2m coiled cable	2m coiled cable	2m coiled cable