

Atlantic, Atlantic-E and Marina: cabinets and equipment selection chart

EXTERNAL DIMENSIONS				ATLANTIC CABINETS (p. 264)	ATLANTIC-E CABINETS (p. 268)	MARINA CABINETS (p. 270)		EQUIPMENT (p. 276)										ADDITIONAL PRODUCTS
				METAL IP 66 - IK 10 (1 door) IP 55 - IK 10 (2 doors) RAL 7035	METAL IP 66 - IK 10 RAL 7035	POLYESTER - IP 66 - IK 10 RAL 7035		Plain plates	Lina 12.5 plates	Perforated plates Lina 25	Sectionned uprights Lina 25	Crosspieces rails	Insulated modular chassis	Internal doors (+Cat.No 0 363 69 for mounting on Atlantic metal cabinets)	Roofs	Plinths	IP 55 Cabstop plate Direct mounting on Atlantic cabinet opening ⁽³⁾	 Hinged glass doors (p. 278)
Shapes	H (mm)	W (mm)	D (mm)															 Kit Cat.No 0 364 98 for mounting Cabstop plate on plain surface (p. 265)
	300	200	150		0 399 30													
	400	300	150		0 399 34													
	400	300	160	0 355 09 ⁽¹⁾														
	500	400	150		0 399 38													
	300	200	160	0 355 00 ⁽¹⁾ supplied with plain plate		0 362 50		0 360 49 ^(M)	0 360 00 ^(A) 0 360 01 ^(M)	0 360 07 ^(A) 0 360 09 ^(M)	0 361 50 ^(A)							
	400	300	200	0 355 02	0 399 35	0 362 51	0 362 71	0 360 52	0 360 04	0 360 12	0 361 51	0 367 80	0 361 01	0 363 59 ^{(A)(M)}	0 365 51 ^{(A)(E)}		0 364 94 ^(A)	 Document pockets (p. 278)
	500	400	200	0 355 03	0 399 39	0 362 52	0 362 72	0 360 55	0 360 09	0 360 15	0 361 52	0 367 81	0 361 02	0 363 60 ^{(A)(M)}	0 365 52 ^{(A)(E)}		0 364 95	
	600	400	200	0 355 04	0 399 42			0 360 56	0 360 22	0 360 16	0 361 53	0 367 81		0 363 61 ^{(A)(M)}	0 365 52 ^{(A)(E)}		0 364 95	
	600	500	200		0 399 44					-	0 361 53	0 367 82					0 364 95	
	700	500	200		0 399 51					0 360 31	0 360 18	0 361 54	0 367 82				0 364 95	
	800	600	200		0 399 54					0 360 33	0 360 19	0 361 55	0 367 83				0 364 95	
	500	400	250	0 355 07	0 399 40			0 360 55	0 360 09	0 360 15	0 361 52	0 367 81		0 363 60 ^{(A)(M)}	0 365 53 ^{(A)(E)}		0 364 95	 Colring cable ties (p. 293)
	600	400	250	0 355 08	0 399 43	0 362 55	0 362 75	0 360 56	0 360 22	0 360 16	0 361 53	0 367 81	0 361 03	0 363 61 ^{(A)(M)}	0 365 53 ^{(A)(E)}		0 364 95	
	600	500	250		0 399 45					-	0 361 53	0 367 82			0 365 64 ^{(A)(E)}		0 364 95	
	700	500	250	0 355 12	0 399 52	0 362 56	0 362 76	0 360 58	0 360 31	0 360 18	0 361 54	0 367 82	0 361 05	0 363 62 ^{(A)(M)}	0 365 64 ^{(A)(E)}		0 364 96 ^(A)	 Heat regulation (p. 282)
	800	600	250	0 355 14	0 399 55			0 360 59	0 360 33	0 360 19	0 361 55	0 367 83		0 363 63 ^{(A)(M)}	0 365 54 ^{(A)(E)}		0 364 97	
	1000	600	250	0 355 17				0 360 54	0 360 40	0 360 23	0 361 56	0 367 83					0 364 97	
	1000	800	250	0 355 18	0 399 64			0 360 61	0 360 42	0 360 21	0 361 56	0 367 84		0 363 64 ^{(A)(M)}			0 364 97	
	700	500	300	0 355 22				0 360 58	0 360 31	0 360 18	0 361 54	0 367 82		0 363 62 ^{(A)(M)}			0 364 96	
	800	600	300	0 355 23	0 399 56	0 362 61	0 362 81	0 360 59	0 360 33	0 360 19	0 361 55	0 367 83	0 361 06	0 363 63 ^{(A)(M)}	0 362 94 ^(M) 0 365 56 ^{(A)(E)}	0 362 91 ^(M) 0 363 00 ^(E)	0 364 97	
1000	600	300	0 355 26	0 399 63			0 360 54	0 360 40	0 360 23	0 361 56	0 367 83			0 365 56 ^{(A)(E)}	0 363 00 ^(E)	0 364 97		
1000	800	300	0 355 27	0 399 65	0 362 63	0 362 83	0 360 61	0 360 42	0 360 21	0 361 56	0 367 84	0 361 09	0 363 64 ^{(A)(M)}	0 362 95 ^(M) 0 365 57 ^{(A)(E)}	0 362 92 0 363 00 ^(E)	0 364 97		
1200	800	300	0 355 92	0 399 69	0 362 64	0 362 84	0 360 64	0 360 46	0 360 27	0 361 58	0 367 84	0 361 10	0 363 65 ^{(A)(M)}	0 362 95 ^(M) 0 365 57 ^{(A)(E)}	0 362 92 0 363 01 ^(E)	0 364 97		
1200	1000	300	0 355 93 ⁽²⁾				0 360 65	0 360 47	0 360 28	0 361 58						2 x 0 364 96		
1400	1000	300	0 355 95 ⁽²⁾				0 360 68	0 360 79	0 360 98	0 361 59						2 x 0 364 96		
800	600	400	0 355 28				0 360 59	0 360 33	0 360 19	0 361 55	0 367 83		0 363 63 ^{(A)(M)}			0 364 97		
1000	800	400	0 355 29				0 360 61	0 360 42	0 360 21	0 361 56	0 367 84		0 363 64 ^{(A)(M)}			0 364 97		
1200	800	400	0 355 96				0 360 64	0 360 46	0 360 27	0 361 58	0 367 84		0 363 65 ^{(A)(M)(3)}			0 364 97		
1400	800	400	0 355 98				0 360 67	0 360 75	0 360 90	0 361 59	0 367 84					0 364 97		
	300	300	150		0 399 31													
	300	300	160	0 355 05 ⁽¹⁾				0 360 69	0 360 02	0 360 91	0 361 50	0 367 80						
	300	300	200	0 355 30	0 399 32			0 360 69	0 360 02	0 360 91	0 361 50	0 367 80					0 364 94	
	400	400	200	0 355 31	0 399 36			0 360 70	0 360 05	0 360 92	0 361 51	0 367 81					0 364 95	 Floor fixing with stands (p. 271)
	500	500	250	0 355 32	0 399 41			0 360 71	0 360 14	0 360 93	0 361 52	0 367 82					0 364 95 ^(E) 0 364 96 ^(A)	
	600	600	250	0 355 10	0 399 46			0 360 57	0 360 24	0 360 17	0 361 53	0 367 83					0 364 97	
	800	800	250	0 355 15				0 360 60	0 360 34	0 360 20	0 361 55	0 367 84					0 364 97	
	600	600	300	0 355 20				0 360 57	0 360 24	0 360 17	0 361 53	0 367 83					0 364 97	
	800	800	300	0 355 24	0 399 59			0 360 60	0 360 34	0 360 20	0 361 55	0 367 84			0 365 57 ^{(A)(E)}	0 363 01 ^(E)	0 364 97	
	1000	1000	300	0 355 91 ⁽²⁾				0 360 63	0 360 43	0 360 25	0 361 56						2 x 0 364 96	 Locking accessories (p. 280)
	1200	1200	300	0 355 94 ⁽²⁾			0 360 66	0 360 48	0 360 89	0 361 58						2 x 0 364 97		
	600	600	400	0 355 36			0 360 57	0 360 24	0 360 17	0 361 53	0 367 83					0 364 97		
	1200	1200	400	0 355 97 ⁽²⁾			0 360 66	0 360 48	0 360 89	0 361 58						2 x 0 364 97		
	300	400	200	0 355 01	0 399 33			0 360 52	0 360 04	0 360 11	0 361 50	0 367 81			0 365 52 ^{(A)(E)}		0 364 95	
	400	600	250	0 355 06	0 399 37			0 360 56	0 360 22	0 360 13	0 361 51	0 367 83			0 365 54 ^{(A)(E)}		0 364 97	
800	1000	250	0 355 33 ⁽²⁾				0 360 61	0 360 42	0 360 94	0 361 55						2 x 0 364 96		
600	800	300	0 355 21 ⁽²⁾				0 360 59	0 360 33	0 360 06	0 361 53	0 367 84					0 364 97		
600	1000	300	0 355 37 ⁽²⁾				0 360 54	0 360 40	0 360 08	0 361 53						2 x 0 364 96		
800	1000	300	0 355 34 ⁽²⁾				0 360 61	0 360 42	0 360 94	0 361 55						2 x 0 364 96	 Marina enclosures RAL 7035 IP 66 - IK 10 (p. 272)	
1000	1200	300	0 355 90 ⁽²⁾				0 360 65	0 360 47	0 360 10	0 361 56						2 x 0 364 97		

1: Without cable entries plate - 2: 2 doors - 3: Usable area: 800 x 640 mm - 4: Crosspieces to be cut (2 m height) can be used for cabinets width 1000 and 1200 (see p. 278)

5: Use kit Cat.No 0 364 98 (p. 265) for direct mounting on Marina cabinets - (A) For Atlantic - (E) For Atlantic-E - (M) For Marina