

2093 Z-94

Ratchet handle with coupler 1/4"

Code	ETIM
6170750	EC002218
EAN	UNSPSC
4010886617076	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	



Article description

- Used throughout industry and the automotive world
- Acc. to DIN 3122, ISO 3315
- With square coupler, medium-fine toothed, extremely rugged
- Return angle 18°
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 6.3, ISO 1174, ball locking device
- Vanadium steel 31CrV3, chrome-plated

Article information

Contents (Qty of pieces)	1	Drive connector square (male)	1/4"
Net weight [kg]	0,076 kg	Drive connector square (male)	6,3 mm
Total length [mm]	130 mm	Return angle	18 °
Total width [mm]	25 mm	Head height 1 [mm]	12 mm
Total height [mm]	20 mm	Handle material	2-components
Surface	chrome-plated	Ratchet head height	12 mm
Material	Chrome-vanadium steel 31CrV3	Shift type	Push-through square
Standard	DIN 3122		
	ISO 3315		