

A646 - Vis-Tex Winter Cut D13 Nitrile Glove

Collection: Cut Resistant

Range: Hand Protection

Materials: HPPE, Glass Fibre, Polyester, Acrylic, Elastic

Dipping:

Inner Pack: 12

Outer Carton: 72

Product information

Providing high risk cut protection even in cold conditions, the Vis-Tex Winter Cut D13 Nitrile Glove combines a HPPE outer layer and acrylic thermal layer. The twin layer design traps in heat and keeps the hands warm and protected from cuts. The design also means that these gloves also provide excellent heat protection.

Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwests' extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 3

EN 388: 2016 + A1: 2018 (4X43D)

EN 407: 2020 (X2XXXX)

EN 511: 2006 (X2X)

ANSI/ISEA 105: 2016 CUT Level (A4)

ANSI/ISEA 105: 2016 ABRASION Level (6)



Features

- Level D cut resistance
- Warm 7 gauge acrylic liner for extreme cold protection
- Specially designed for use in cold conditions
- Flexible sandy nitrile coating offers great grip in wet and dry conditions
- Double dipped coating for durability
- Provides contact heat protection up to 250°C for 15 seconds
- Available in sizes up to 3XL
- ANSI cut level A4
- CE certified
- Retail tag which aids presentation for retail sales
- Robust 7 gauge liner



PRODUCT SPECIFICATION & TECHNICAL DATASHEET

A646 - Vis-Tex Winter Cut D13 Nitrile Glove Commodity Code: 6116102091

Test House

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
SATRA Technology Park
NN16 8SD, United Kingdom
Cert No: 2777/18209-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
SATRA Technology Park
NN16 8SD, United Kingdom
Cert No: AB0321/18889-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
A646O8RS	Orange/Black	46.0	29.0	53.0	0.1180	0.0707	5036108321667	25036108810431
A646O8RM	Orange/Black	46.0	29.0	53.0	0.1100	0.0707	5036108321650	25036108810424
A646O8RL	Orange/Black	46.0	29.0	53.0	0.1120	0.0707	5036108321643	25036108810417
A646O8RXL	Orange/Black	46.0	29.0	53.0	0.1720	0.0707	5036108321674	25036108810448
A646O8RXXL	Orange/Black	46.0	29.0	53.0	0.1710	0.0707	5036108328871	25036108817669
A646O8RXXXL	Orange/Black	46.0	29.0	53.0	0.1720	0.0707	5036108321681	25036108810455