

Roof outlet filter, Extract: W: 292 mm, H: 292 mm, RAL 7035, IP54,



Model		
product brand name	SIVACON	
product designation	outlet filter for roof mounting	
type of ventilation	ventilation	
fan design withdrawable fan	No	
design of the product EMC version	No	
General technical data		
cutout width	292 mm	
cutout height	292 mm	
Protection class		
protection class IP	IP54	
Appearance		
color	light grey	
Product details		
product component fan	No	
Mechanical Design		
height	361 mm	
width	361 mm	
depth	96 mm	
fastening method	snap-on mounting	
fastening method		
• 19-inch installation		
• wall mounting	No	
net weight	1.1 kg	
material	plastic	
ambient temperature during operation		
• minimum		
• maximum		
-10 °C		
55 °C		
Approvals Certificates		
General Product Approval	other	Environment



[Confirmation](#)

[Environmental Con-
firmations](#)

Further information	
Information on the packaging	
https://support.industry.siemens.com/cs/ww/en/view/109813875	
Information- and Downloadcenter (Catalogs, Brochures,...)	

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6400-5VE67>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6400-5VE67>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6400-5VE67

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

