

## FEATURES

- 5 pieces ESD pliers set:
- 1 micro short needle-nose pliers. ESD-safe version
- 1 flush micro cutter, max cut  $\varnothing$  0.81mm - 20 awg. ESD-safe version
- 2 precision screwdrivers:  
1 slot tip  $\varnothing$  2.5mm, 2.5x75mm, 175mm total length; 1 phillips tip  $\varnothing$  2.5mm, PH-00 2.5x60mm, 160mm total length ESD-safe version
- 1 ESD tweezers: model 7 very fine curved tips
- In durable ESD wallet roll
- Ergonomic anti-slip bi-component handle for a safe, light and comfortable grip
- Anti-reflection phosphating surface treatment
- Laser marking
- Made in Italy

## RS PRO 5 pieces ESD set: 1 micro pliers, 1 micro cutter, 2 precision screwdrivers, 1 tweezers

RS PRO Stock No.: 249-8657



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

### Product Description

- *Made in Italy with special carbon steel and undergo a controlled atmosphere heat treatment.*
- *The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.*
- *The tools are joined with grounded holes and surfaces, thereby allowing precise movements.*
- *The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours*
- *This tools set is ideal for different applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY. In durable ESD wallet roll*

### General Specifications

<b>1 ESD SHORT NEEDLE NOSE PLIERS</b>	
<b>Non-Sparking</b>	Yes
<b>Tip Style</b>	Short micro needle-nose pliers
<b>Material</b>	Carbon steel
<b>Finish</b>	Anti-reflection phosphating surface treatment, grey grip
<b>Overall Length</b>	136 mm
<b>HRC</b>	48-50
<b>Weight</b>	60 g
<b>Steel Thickness</b>	2 mm
<b>1 ESD MICRO CUTTER</b>	
<b>Cutter Type</b>	Micro head. Flush cut.
<b>Non-Sparking</b>	Yes
<b>Tip Style</b>	Flush cut. Micro head size
<b>Material</b>	Carbon steel
<b>Finish</b>	Anti-reflection phosphating surface treatment, grey grip
<b>Overall Length</b>	132 mm
<b>Cutting Force</b>	3.0 kg
<b>Steel Thickness</b>	2.0 mm
<b>Max cut</b>	Ø 0.81mm - 20 awg copper wire
<b>1 ESD PRECISION SCREWDRIVER SLOTTED</b>	
<b>Overall length (mm)</b>	175
<b>Blade dimensions length (mm)</b>	2.5x75mm
<b>Tip diameter</b>	Ø 2.5mm
<b>Point Type</b>	slotted

<b>1 ESD PRECISION SCREWDRIVER PHILLIPS</b>	
<b>Overall length (mm)</b>	160
<b>Blade dimensions length (mm)</b>	PH-00 2.5x60mm
<b>Tip diameter</b>	Ø 2.5mm
<b>Point Type</b>	phillips
<b>1 ESD TWEEZERS MODEL 7 ESD</b>	
<b>Overall length (mm)</b>	120
<b>Overall length (“)</b>	4 3/4”
<b>Point Type</b>	very fine curved tips
<b>Anti-magnetic</b>	Yes
<b>Anti-acid</b>	Yes

### Electrical Specifications

<b>ESD Safe</b>	YES
-----------------	-----

### Kit contains

Name	QTY	RSPRO order code
<b>ESD micro needle-nose pliers</b>	1	249-8673
<b>ESD flush cutter- micro head</b>	1	238-0814
<b>ESD precision screwdriver slotted</b>	1	249-8665
<b>ESD precision screwdriver phillips</b>	1	249-8663
<b>ESD tweezers international code 7</b>	1	238-0708

