

Note:
- Drawings Not To Scale
- Drawings Subject to Change Without Notice
- Dimensions are inches next to [Millimeters]

Part No.:

XSAV11373L05



Specification:

Telemecanique Sensors 1875 Founders Drive Dayton, OH 45420-4017 Customer Care Center : 1-800-435-2121 Web: www.tesensors.com

Technical Information:

Detecting Distance:
Circuit Type:
Output Mode:
Volts Type:
Voltage Range:
Max Load:
Shielding:
Max Switching Frequency:
Temp Range:
NEMA Type:
IP Rating:
Standards: 10.0 mm (0.39 in) PNP NO DC 12-24 VDC 200 mA Shielded

6000 Hz

-25° to 70° C (-13° to 158° F) 4X (indoor use only) IP67

UL, CE Rohs

Proximity Sensor, Inductive, 30 mm Barrel, 12-24 VDC, Shielded

Barrel

Sensor Type:
Description:
Body Style:
Diameter:
Housing Material:
Cable Size:
Connector Type:
Special Features: mm Nickel Plated Brass 5.0 m (16.4 ft)

Motion Detection Sensor