

# 2U Vented Center-Mount Shelf - 14/20 in. Depth

## **Product IDs**

SHELF-2U-14-CENTER-V SHELF-2U-20-CENTER-V

# **Product Diagram**

Front - Angled View



\*Product may vary from image

Component		Function
1	Shelf Lip	<ul> <li>Mount the 2U Vented Center-Mount Shelf with the Shelf Lip oriented upwards to prevent Equipment from slipping off</li> </ul>
2	Mounting Holes (x 8)	<ul> <li>Mount the 2U Vented Center-Mount Shelf into a Rack.</li> </ul>

# **Product Information**

For the latest manuals, product information, technical specifications, and declarations of conformance, please visit:

www.StarTech.com/SHELF-2U-14-CENTER-V www.StarTech.com/SHELF-2U-20-CENTER-V

## Requirements

- 2U Available Rack Space
- Phillips Head Screwdriver
- (Optional) Cage Nut Tool

## Warnings

- Read the entire manual and ensure the instructions are fully understood before assembling and/or using this product.
- Before adding equipment to this product, ensure this product has been properly mounted.
- Ensure the weight of the equipment does not exceed the weight capacity of this product. If the weight capacity is exceeded, personal injury or damage to the equipment are possibilities. This product can support the following weight: up to 200.6 lb. (91 kg). This product can only support the maximum weight capacity if 8 M6 Screws / Cage Nuts / Plastic Washers are used to affix this product to a rack.

## **Package Contents**

- 2U Vented Center-Mount Shelf x 1
- M6 Cage Nuts x 10
- M6 Screws x 10
- M6 Plastic Washers x 10
- Quick-Start Guide x 1

## Installation

Mount the 2U Vented Center-Mount Shelf into a Rack

Use the included M6 Cage Nuts, M6 Screws, and M6 Plastic Washers to install the 2U Vented Center-Mount Shelf.

Notes: This product can support the following weight: 200.6 lb. (91 kg).

The following installation instructions are for square mounting holes.

1. Locate a suitable location in a Rack to mount the 2U Vented Center-Mount Shelf.

Note: The 2U Vented Center-Mount Shelf itself requires 2U of space within a Rack.

- 2. Insert the Wing (side) of an M6 Cage Nut into the back of the a Cage Nut Hole.
- 3. Insert the second **Wing** of the **M6 Cage Nut** into the selected **Cage Nut Hole**, using pressure by hand, or with a **Cage Nut Tool**.
- 4. Repeat steps 2 and 3 to insert a total of 8 Cage Nuts.
- 5. Thread an M6 Plastic Washer over an M6 Screw. Repeat until 8 M6 Screw Assemblies have been prepared.

- 6. Align the Mounting Holes in the 2U Vented Center-Mount Shelf with the M6 Cage Nuts installed in steps 2-4.
- 7. Insert the M6 Screw Assemblies through the Mounting Holes in the 2U Vented Center-Mount Shelf and into the M6 Cage Nuts and tighten, using a Phillips Head Screwdriver.

### **Regulatory Compliance**

#### Use of Trademarks, Registered Trademarks, and other Protected Names and Symbols

This manual may make reference to trademarks, registered trademarks, and other protected names and/or symbols of thirdparty companies not related in any way to StarTech.com. Where they occur these references are for illustrative purposes only and do not represent an endorsement of a product or service by StarTech.com, or an endorsement of the product(s) to which this manual applies by the third-party company in question. StaTech.com hereby acknowledges that all trademarks, registered trademarks, service marks, and other protected names and/or symbols contained in this manual and related documents are the property of their respective holders.

PHILLIPS® is a registered trademark of Phillips Screw Company in the United States or other countries.

### Warranty Information

This product is backed by a lifetime warranty. For further information on product warranty terms and conditions, please refer to www.startech.com/warranty.

#### Limitation of Liability

In no event shall the liability of StarTech.com Ltd. and StarTech.com USA LLP (or their officers, directors, employees or agents) for any damages (whether direct or indirect, special, punitive, incidental, consequential, or otherwise), loss of profits, loss of business, or any pecuniary loss, arising out of or related to the use of the product exceed the actual price paid for the product. Some states do not allow the exclusion or limitation of incidental or consequential damages. If such laws apply, the limitations or exclusions contained in this statement may not apply to you.

StarTech.com Ltd. 45 Artisans Crescent London, Ontario N5V 5E9 Canada

Road

43125

U.S.A.

StarTech.com LLP 4490 South Hamilton Groveport, Ohio Brackmills, Northampton NN4 7BW

StarTech.com Ltd. StarTech.com Ltd. Unit B, Pinnacle 15 Siriusdreef 17-27 2132 WT Hoofddorp Gowerton Road The Netherlands United Kingdom

FR: startech.com/fr DE: startech.com/de ES: startech.com/es NL: startech.com/nl IT: startech.com/it JP: startech.com/jp