

QUICK SET PLIERS WRENCH 10"



- Eliminates the need for multiple spanner sets, offering a convenient all-in-one solution
- Ideal for damage-free work on plated fittings, preventing marring or scratching
- Versatile in function, capable of gripping, holding, pressing, and bending
- Parallel jaws design ensures a solid and consistent grip across various applications

The TengTools 10-inch quick set pliers wrench MB483-10 is a highly versatile tool tailored for professionals in fields such as automotive repair, plumbing, and general maintenance. This tool effectively eliminates the need for multiple sets of mm and inch spanners, making it a practical asset in any toolkit. Its design prevents surface damage when working with delicate, plated pipe fittings. The tool's capabilities extend to gripping, holding, pressing, and bending. The parallel jaws are engineered for a firm and consistent grip, providing increased control and efficiency.

General information

Country of origin: Taiwan
Barcode: 5020385053236
Tariff code Europe: 8203200000
ECCN US: EAR99
UNSPSC: 27112111

Attributes

Product type: Adjustable Wrenches
Capacity (mm): 45
Tethering facility: No
Jaw depth (mm): 35

Dimensions

Net weight (g): 422
Length: 250 mm
Length 2: 10"

Technical changes and errors may occur. 01-08-2024 20:00



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden