

Cable duct - CD 40X100 - 3240294

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Cable duct, gray, consisting of upper and lower part, width: 40 mm, height: 100 mm, length 2000 mm

Product Features

- ✓ Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- ✓ Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- ✓ Predetermined breaking point enables tool-free, burr-free removal of bars
- ✓ The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- ✓ Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- ✓ Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Key commercial data

Packing unit	1 PCE
Minimum order quantity	20 PCE
GTIN	 4 046356 481359
Custom tariff number	39259020
Country of origin	GERMANY

Technical data

General

Length (b)	2000 mm
Height	100 mm
Width (a)	40 mm
Color	gray
Inflammability class according to UL 94	V0
Ambient temperature (operation)	-5 °C ... 60 °C
Components	Lead-free
Material	PVC

Cable duct - CD 40X100 - 3240294

Classifications

ETIM

ETIM 2.0	EC000012
ETIM 3.0	EC000012
ETIM 4.0	EC000012
ETIM 5.0	EC000012

UNSPSC

UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708
UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708

eCl@ss

eCl@ss 4.0	27140602
eCl@ss 4.1	27140602
eCl@ss 5.0	27140602
eCl@ss 5.1	27140602
eCl@ss 6.0	27400703
eCl@ss 7.0	27400703