

blanking plug B-1/2

Part number: 3571

★ Core product range

FESTO



Data sheet

Feature	Value
Container size	10
Conforms to standard	DIN 908
Nominal tightening torque	14 Nm
Tolerance for nominal tightening torque	± 20 %
Product weight	43 g
Mounting type	Internal hex A/F 10
Pneumatic connection, port 1	Male thread G1/2
Materials note	Free of copper and PTFE Conforms to RoHS
Material blanking plug	Galvanised steel
Material o-ring	PA TPE-U(PUR)