



Cut

Abrasion Protection



Medium Duty

Highly cut-resistant arm protection sleeves, featuring advanced compression technology

- **Advanced protection:** HyFlex® 11-290 protective arm sleeves are designed with INTERCEPT™ Cut Resistance Technology, offering ANSI/ISEA 105-2024 CUT A5 and EN ISO E protection against lacerations
- **Optimized safety:** With nine compression zones* to regulate pressure levels, these protective sleeves boost blood circulation, stabilize arm muscles and improve workplace safety
- **Improved ergonomics:** Their ergonomic design results in a natural, contoured fit
- **Elevated comfort:** Made from breathable material, these HyFlex® protective sleeves ensure all-day comfort
- **Specialized defenses:** Their thermo-resistant fibers guard against heat up to 100°C/212°F (EN 407 contact heat protection level 1)
- **Enhanced features:** They include an integrated elbow pad, for impact protection and added longevity
*high cut compression, tested to DIN SPEC 4868 standards



Industries

- Automotive
- Automotive Aftermarket
- Aerospace
- Machinery and Equipment
- Metal fabrication
- Construction

Applications

- Glass repair and replacement
- Handling metal sheets & panels
- Equipment maintenance and repair
- Assembly of parts

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-290

High Cut High Comfort Sleeve with a Compression Profile

Key Features

- **INTERCEPT™ Technology:** ANSI/ISEA 105-2024 CUT A5 and EN ISO E protection
- **Nine compression zones*:** Better blood circulation, stabilized muscle tension
- **Ergonomic design with breathable material:** Excellent fit and comfort

*high cut compression, tested to DIN SPEC 4868 standards

Technologies

 **INTERCEPT™**
Cut Resistance Technology

 **Kevlar®**

 **ZONZ™**
Comfort Fit Technology

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



3X42E

EN 407



X1XXXX



Specifications

BRAND STYLE	DESCRIPTION	Gauge	LENGTH	PACKAGE
HyFlex® 11-290	Liner Material: Kevlar®, Stainless steel, Polyamide, Spandex Cuff Style: Knitwrist	15	45cm	30 pieces/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2025 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

