

Rittal – The System.

Faster – better – everywhere.

► Baying enclosure system VX25 Basic enclosure – VX 8886.000

Date : Jun 18, 2019

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Baying enclosure system VX25 Basic enclosure – VX 8886.000

created: 18.06.2019 on www.rittal.com/com-en



Product description

| | |
|--|--|
| Material: | Enclosure frame: Sheet steel, 1.5 mm Roof: Sheet steel, 1.5 mm Door: Sheet steel, 2.0 mm Rear panel: Sheet steel, 1.5 mm Gland plates: Sheet steel, 1.5 mm Mounting plate: Sheet steel 3.0 mm |
| Surface finish: | Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint |
| Colour: | RAL 7035 |
| Protection category IP to IEC 60 529: | IP 55 |
| Protection category NEMA: | NEMA 12 |
| Type rating to UL 508A: | Type 1,12 |
| IK Code: | IK10 |
| Supply includes: | Enclosure frame Door(s) Door hinged on the right, may be swapped to the left Roof plate Rear panel Gland plates Mounting plate 2 punched rails 18 x 39 mm Lock: 3 mm double-bit |

Basic material: Sheet steel

Product features

Dimensions: Width: 800 mm
Height: 1800 mm
Depth: 600 mm

Mounting plate: Width: 699 mm
Height: 1696 mm

Number of doors: 1

Packs of: 1 pc(s).

Weight/pack: 125.8 kg

EAN: 4028177813946

Customs tariff number: 94032080

ETIM 6.0: EC000261

ETIM 5.0: EC000261

eCl@ss 8.0/8.1: 27180101

eCl@ss 7.0/7.1: 27180101

eCl@ss 6.0/6.1: 27180101

eCl@ss 5.1/5.1.4: 27180101

Product description: VX Baying enclosure system, WHD: 800x1800x600 mm, sheet steel, with mounting plate, single door at the front

Approvals

Approvals: CSA
Lloyds Register of Shipping
UL + C-UL

Certificates: EAC
Protection category

Declarations: Declaration of conformity