

## 622N, E622N "N" Series Cutters



- Small oval head, full flush

Cat No.	UPC No.	Packed	Length		Max. Cutting Dia.		Dimension "A"		Shelf Pack
			Inch	mm	Inch	mm	Inch	mm	
622N	RS 270-8510 3127132056	Boxed	4.25	108	.05	1.3	.354	9	1
622NV	043127144288	Carded	4.25	108	.050	1.3	.394	10	6
*E622N	043127132117	Boxed	5.75	147	.05	1.3	.354	9	1

## 622NA, 622NB "N" Series Cutters



- 622NA tapered head, full flush
- 622NB tapered relieved head, full flush

Cat No.	UPC No.	Packed	Length		Max. Cutting Dia.		Dimension "A"		Shelf Pack
			Inch	mm	Inch	mm	Inch	mm	
622NA	043127155320	Boxed	4.25	108	.050	1.3	.394	10	1
622NB	RS 420-5748 43127155337	Boxed	4.25	108	.050	1.3	.394	10	1

## 632N, E632N "N" Series Cutters



- Small head, super full flush

Cat No.	UPC No.	Packed	Length		Max. Cutting Dia.		Dimension "A"		Shelf Pack
			Inch	mm	Inch	mm	Inch	mm	
632N	043127137051	Boxed	4.25	108	.050	1.3	.394	10	1
632NV	043127144257	Carded	4.25	108	.050	1.3	.394	10	6
*E632N	043127137044	Boxed	5.75	147	.050	1.3	.394	10	1

\* Ergonomic version