

Datasheet

RS Pro High Power Inspection Lamp (UK Plug)

RS Stock No: 111-7926



Features:

- * Ideal for inspections, from workshops to outdoor.
- * Recharge from the convenient docking station via AC adapter or USB wire.
- * It could be fixed by special side belt clip or powerful magnet or swivel hook.
- * LED will blink to indicate charging and illuminate blue when fully charged.



ENGLISH

Specification:

- * Rating : input – AC:100 ~ 240V / DC: USB 2.0, output - 5V/1A
- * LED: SMD 0.5W, 8 pcs, white (5700K)
- * Max luminance : 215 Lux at 50 cm
- * Battery : Li-ion 3.7V 2200 mAh rechargeable.(3.5 hours fully charging for lasting 5 hours.)
- * Operating temperature: -20°C ~ +60°C
- * Size: 34.4(L) x 32.2(W) x 187.6(H) mm