

Digital indicator with data output and IP54 protection.

Features

- Large LCD display on 58mm diameter dial face
- Functions: ABS/INC (absolute and incremental modes), mm/inches, tolerance setting, zero and offset setting
- IP54 Ingress Protection
- 8mm/H7 clamping diameter
- Configurable as lugback and flat back



Specification

Code No	Range (mm)	Range (inch)	Resolution (mm)	Resolution (inch)	Accuracy (mm)	Accuracy (inch)
MW430-01DABS	0-12.5	0-0.5	0.001	0.00005	±0.004	±0.0002
MW430-02DABS	0-25.4	0-1.0	0.001	0.00005	±0.005	±0.00025
MW430-03DABS	0-50.8	0-2.0	0.001	0.00005	±0.006	±0.0003