



Product data sheet

Power tools for trade & industry

Cordless Jobsite Light

PRO GLI 18V-2200 C



The versatile and robust floodlight with 2,200 lumens in the 18 V category - connected

The most important data

Battery voltage, works with	18.0 V
Luminous flux	2,200 lm
Weight excl. battery	1.9 kg

Part Number 0 601 446 501

Technical data

Technical data

Weight excl. battery	1.9 kg
Luminous flux	2,200 lm
Max. operating time 14.4 V	80 mins/Ah
Max. operating time 18 V	100 mins/Ah
Number of brightness levels	2
Packaging dimensions (width x length x height)	187 x 176 x 271 mm
Battery voltage, works with	18.0 V



BOSCH

Invented for life

Product data sheet

Power tools for trade & industry

Advantages:

- Powerful LED is capable of producing up to 2,200 lumens for superior lighting conditions
- Splash-proof and dust-tight due to an IP 64-rated, robust battery cover
- Convenient smartphone control for fast and easy remote lighting adjustments; 2 brightness settings, 5 adjustment angles



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

