



PIN OUT

P1	P2	Color	FAM
1	2	BLUE	RED FAM
3	1	WHITE	
2	3	DRAIN	
4	10	BLUE	SILVER FAM
6	9	WHITE	
5	11	DRAIN	
7	18	BLUE	BLUE FAM
9	17	WHITE	
8	19	DRAIN	
10	23	BLUE	BROWN FAM
12	24	WHITE	
11	22	DRAIN	
15	6	RED	
16	7	WHITE	
17	15	YELLOW	
18	14	ORANGE	
19	16	PURPLE	

SHELL DRAIN SHELL

NOTES:

1. MATERIAL

- 1.1 HDMI CABLE: (7/0.10TC*1P+7/0.10TC+FAM)*4PCS+7/0.12TC*3C+7/0.12TC*1P+AL+7/0.12TC+128/0.12ALM+BLACK PVC JACKET.
OD: $\varnothing 6.0 \pm 0.2$ mm
- 1.2 HDMI 19PIN TYPE A MALE : BLACK INSULATION, GOLD PLATED CONTACTS, NICKEL PLATED SHELL.
- 1.3 DVI(18+1) MALE: BLACK INSULATION, GOLD PLATED CONTACTS G/F, NICKEL PLATED SHELL.
- 1.4 THUMB SCREW TO BE MOLDED BLACK PVC. NICKEL PLATED SCREW.
- 1.5 ALL HOOD: MOLDED BLACK PVC.

2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
- 2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
- 2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
- 2.4 HI-POT: DC300V/0.01S.

3. PACKAGING: A PC/PE-BAG PACKAGING .

4. ALL MATERIALS ARE REACH COMPLIANT.

P/N	L(mm)
11.99.5519	1000±30mm
11.99.5522	2000±50mm
11.99.5532	3000±70mm
11.99.5552	5000±70mm



REV.	MODIFY DESCRIPTION	DATE
02	ADD THE ONE	2012-01-05
01	CHANGE THE CABLE MARKING	2011-02-23
00	NEW ISSUE	2010-03-16

LENGTH TOLERANCE: X. ± 0.5 .X ± 0.2 .XX ± 0.1	SCALE: FREE		VALUE DVI Cable, DVI M-HDMI M, black
ANGLE TOLERANCE: X' ±3' .X' ±1'	UNIT: mm		
	VERSION: 02	PAGE: 1/1	

ENG:
CHECKED:
APPROVED: