



Main

| | |
|-------------------|----------------------------|
| Enclosure type | Weatherproof enclosure |
| Range of product | Kaedra |
| Device short name | Kaedra versatile enclosure |

Complementary

| | |
|------------------------------|-------------------------------------|
| Enclosure mounting | Surface |
| Type of front cover | Opaque Reversible |
| Number of pre-cutouts PG ISO | 17 |
| Locking options description | Optional keylock |
| Enclosure material | Plastic |
| Width | 340 mm |
| Height | 460 mm |
| Depth | 160 mm |
| Colour | Enclosure : light grey (RAL 7035) |

Environment

| | |
|---------------------------------------|---|
| Standards | EN 50102 EN 50262 IEC 60439-3 IEC 60529 IEC 670 |
| Fire resistance | 750 °C |
| IP degree of protection | IP65 conforming to IEC 60529 |
| IK degree of protection | IK09 conforming to EN 50102 |
| Electrical shock protection class | Class II |
| Ambient air temperature for operation | -25...60 °C |
| RoHS EUR conformity date | 0622 |
| RoHS EUR status | Compliant |