

Main

Range of product	Odace
Range	Odace
Product or component type	Loudspeaker socket
Device presentation	Mechanism with fixing frame
Type of packing	Paint cover
Quantity per set	Set of 5

Complementary

Device mounting	Flush
Socket number	2
Fixing mode	By screws
Colour tint	Anthracite
Surface finish	Matt
Number of terminals	4 screwless terminals
Number of loop terminals	1
Clamping connection capacity	4 x 1.5...4 x 2.5 mm ² for rigid cable(s) 4 x 1.5...4 x 2.5 mm ² for stranded cable(s) 4 x 1.5...4 x 2.5 mm ² for flexible cable(s)
Wire stripping length	12 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame PA (polyamide) 6 GF20 FR: casing
Height	71 mm
Width	71 mm
Depth	47.2 mm
Embedding depth	19.9 mm
Net weight	0.038 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
IK degree of protection	IK04

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	 China RoHS Declaration
RoHS exemption information	 Yes