

## DATASHEET



### SUR5LED SUR5LEDEM

### 45W LED SURFACE MOUNTED PANEL

[www.mlaccessories.co.uk](http://www.mlaccessories.co.uk)

MLA PART CODE	SUR5LED	SUR5LEDEM
DESCRIPTION	45W Surface Mounted LED Panel	45W Surface Mounted Emergency LED Panel
FINISH	White	
NETT WEIGHT (KG)	3.25	3.5
DIMENSIONS (MM)	Length – 1500 Width – 200 Projection – 45	
WATTAGE (W)	45	
LUMENS (LM)	4790 ±5%	
EFFICACY (LM/W)	106	
LUMENS EMERGENCY MODE (LM)	N/A	190 ±5%
CCT	4000K	
LED COLOUR	Cool White	
CRI	>80	
CIRCUIT WATTAGE (W)	45	
RUNNING CURRENT (A)	0.19	
POWER FACTOR	0.98	
BEAM ANGLE	110°	
LIFE SPAN (HRS)	50,000 Hrs	
INPUT VOLTAGE	Mains 230V 50Hz	
CONSTRUCTION	Pressed Steel	
CLASS	Class I	
IP RATING	IP20	
DIMMABLE	No	
WARRANTY	5 Years (excluding battery)	
ORIGIN OF MANUFACTURE	China	
DECLARATION OF CONFORMITY (HELD ON FILE)	Yes	
MANUFACTURED IN ACCORDANCE WITH	BS EN 60598, BS EN 60598-2-22	
EAN	5056270821550	5056270821598



AVNOV20\_V1