

Housing - HC-STA-B24-BWS-ELC-AL - 1411329

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON B24 panel mounting base, with single locking latch, with flat gasket, salt-water-resistant aluminum, conductive profile gasket



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 927499
Weight per Piece (excluding packing)	135.7 g
Custom tariff number	85389099
Country of origin	China

Technical data

Dimensions

Height	30.5 mm
Width	53 mm
Length	140.5 mm
Length of the assembly cutout	113 mm
Width of the assembly cutout	35 mm

Ambient conditions

Degree of protection of housing (IP)	IP66
	IP69K (ISO 20653:2013-02)
Degree of protection of housing (NEMA)	4
	4X
	12
Ambient temperature (operation)	-40 °C ... 125 °C

General

Housing - HC-STA-B24-BWS-ELC-AL - 1411329

Technical data

General

Note	For contact inserts HC-B24, BB46, D64, DD108, M
Type	B24
Housing type	Panel mounting base
Locking type	With single locking latch
Torque	1.5 Nm ... 2 Nm (Mounting screw)
Screw connection	none
Housing material	Die-cast aluminum, corrosion resistant
Housing surface material	Uncoated
Material lock	Polyamide

Classifications

eCl@ss

eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 8.0	27440202

ETIM

ETIM 4.0	EC000437
ETIM 5.0	EC000437

Approvals

Approvals

Approvals

EAC / GL

Ex Approvals

Approvals submitted

Approval details


EAC

GL

Drawings


Housing - HC-STA-B24-BWS-ELC-AL - 1411329

Dimensioned drawing



Dimensional drawing

Dimensioned drawing



Panel cutout