

## Han U Protect Cover Die Cast for Base



Image is for illustration purposes only. Please refer to product description.

Part number	09 36 003 5406
Specification	Han U Protect Cover Die Cast for Base
HARTING eCatalogue	<a href="https://harting.com/09360035406">https://harting.com/09360035406</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> Ex
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings With fixing cord

### Version

Size	3 A
Locking type	Single locking lever
Details	for mounted male insert
Details	ATTENTION! Only to be used with Han <sup>®</sup> Ex hoods and housings!

### Technical characteristics

Limiting temperature	-20 ... +40 °C
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 5015 (sky blue)
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Commercial data

Packaging size	10
Net weight	21.8 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140054769
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467