

10429500	DATA SHEET	
Valid from: 25.08.2021	EPIC® H-A 3 MTGVB	

Description

- Innovative metal housing
- For safe connections in the smallest possible space

General characteristics

Series	H-A 3
Version	Cable coupler hood
Locking mechanism	Single lever
Cable entry	Straight
Cable gland	See table
Clamping range	See table
Protection rating (DIN EN 60529)	IP 66 (latched) IP 68 - 1 meter / 10 hours (latched)
Protection rating (NEMA 250, UL50E)	4, 12 (latched)
Temperature range	-40 °C to +100 °C, short-term up to +125 °C



Materials and surfaces

Housing, base material	Zinc die-casting
Housing, surface	Powder-coating, grey
Pressure screw	Brass, nickel-plated
Pressure washer	Steel, zinc-plated
Incised sealing ring	NBR
Lever	Steel, zinc-plated

Standards

Safety Standard	IEC 61984
-----------------	-----------

Approvals

cURus and VDE in preparation.


Versions

Article number	Article description	Thread	Cable gland	Clamping range	Dimension C
10512900	EPIC® H-A 3 MTGVB 11 N.GEW. CABLE COUPLER HOOD	Pg 11	No	-	53,5
10429500	EPIC® H-A 3 MTGVB 11 KPL. CABLE COUPLER HOOD	Pg 11	Yes	6,5 – 12 mm	60
19512900	EPIC® H-A 3 MTGVB M20 N.GEW. CABLE COUPLER HOOD	M20	No	-	53,5
19429500	EPIC® H-A 3 MTGVB M20 KPL. CABLE COUPLER HOOD	M20	Yes	3 – 13,5 mm	61

Creator: TODV1/PDP Released: VACH1/PDP	Document: DB10429500EN Version: 02	Page 1 of 2
---	---------------------------------------	-------------

10429500	DATA SHEET	
Valid from: 25.08.2021	EPIC® H-A 3 MTGVB	

Drawings



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof

Info

Compact, robust metal housings size H-A 3

Application range

Machine and equipment manufacturing
Control engineering
Electronic laboratory

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/PDP Released: VACH1/PDP	Document: DB10429500EN Version: 02	Page 2 of 2
---	---------------------------------------	-------------