




Technical data

7210BG

Single row or matched pairs of angular contact ball bearings

Angular contact ball bearings, pressed steel cage

VISUAL (S)



7210BG

Single row or matched pairs of angular contact ball bearings

PRODUCT DEFINITION

Brand	NTN
d - Internal diameter	50 mm
D - External diameter	90 mm
B - Bearing/Inner ring width	20 mm
a - Charge load application point	39,5 mm
- Contact angle	40 °
rs - Min fillet radius	1,1 mm
r1s - Min fillet radius	0,6 mm
Radial clearance class	CN
Mass	0,466 kg

PRODUCT PERFORMANCE

C - Dynamic load	41500000 mN
C0 - Static load	28600000 mN
Cu - Fatigue limit load	2160000 mN
N lim - Oil lubrication limit speed	54000 °/s
N lim - Grease lubrication limit speed	40200 °/s
Tmin - Min operating temperature	233,15 °K
Tmax - Max operating temperature	393,15 °K

ABUTMENT

da min - Min shoulder diameter IR	57 mm
db min - Min IR shoulder diameter	54,5 mm
Da max - Max shoulder diameter OR	83 mm
Db max - Max OR shoulder diameter	85,5 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

7210BG

Single row or matched pairs of angular contact ball bearings

ABUTMENT

r1a - Max fillet radius	0,6 mm
ra max - Max shaft & housing fillet radius	1 mm

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

	e	Single or DT bearing arrangement				DB or DF arrangement			
		Fa / Fr ≤ e		Fa / Fr > e		Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y	X	Y	X	Y
30°	0.8	1	0	0.9	0.76	1	0.78	0.63	1.24
40°	1.14			0.35	0.57		0.55	0.57	0.93

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

a	Single or DT bearing arrangement		DB or DF arrangement	
	X ₀	Y ₀	X ₀	Y ₀
30°	0.5	0.33	1	0.66
40°		0.26		0.52

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15