



- For any drilling and screwdriving task
- Highly efficient for professionals in various trades: Robust
- Designed for drills



| PRODUCT PROPERTIES                                                                                                                       |              |                   |                         |              |                  |                   |                         | ORDERING INFORMATION |                |               |                        |               |               |
|------------------------------------------------------------------------------------------------------------------------------------------|--------------|-------------------|-------------------------|--------------|------------------|-------------------|-------------------------|----------------------|----------------|---------------|------------------------|---------------|---------------|
| Only for spindle lock                                                                                                                    | R/L rotation | Locking mechanism | Ben drive-mounted drill | Impact-proof | TC clamping jaws | Chuck capacity mm | Mount, range            | Illustration, No.    | Packaging type | Pack quantity | Minimum order quantity | Barcode       | Part number   |
| Suitable for PSR 2.4 V; PSR 3.6 V                                                                                                        |              |                   |                         |              |                  |                   |                         |                      |                |               |                        |               |               |
| •                                                                                                                                        |              |                   |                         |              |                  | 1.0-6.0           | 1/4" external hex shank | 2                    | P1h            | 1             | 1                      | 3165140085434 | 2 608 572 072 |
|                                                                                                                                          | •            |                   |                         | •            |                  | 1.0-10.0          | 3/8" - 24               | 5                    | P1h            | 1             | 1                      | 3165140092036 | 2 608 572 068 |
|                                                                                                                                          | •            |                   |                         |              |                  | 1.0-10.0          | 1/4" external hex shank | 3                    | P1h            | 1             | 1                      | 3165140085441 | 2 608 572 075 |
|                                                                                                                                          | •            | •                 |                         | •            |                  | 2.0-13.0          | 1/2" - 20               | 3                    | C1a            | 1             | 1                      | 3165140064682 | 2 608 572 034 |
| •                                                                                                                                        | •            |                   |                         |              |                  | 2.0-13.0          | 1/2" - 20               | 4                    | P1h            | 1             | 1                      | 3165140082754 | 2 608 572 062 |
| Keyless chuck, chrome-plated                                                                                                             |              |                   |                         |              |                  |                   |                         |                      |                |               |                        |               |               |
| Suitable for GSB 13 RE; GSB 16; GSB 16 RE; GSB 18-2 RE; GSB 19-2 RE; GSB 20-2; GSB 650 RE; GSB 1600 RE Professional; PSB 450; PSB 550 RE |              |                   |                         |              |                  |                   |                         |                      |                |               |                        |               |               |
|                                                                                                                                          |              |                   |                         |              |                  | 1.5-13.0          | 1/2" - 20               | -                    | P1h            | 1             | 1                      | 3165140223416 | 2 608 572 149 |
| SDS plus keyless chuck                                                                                                                   |              |                   |                         |              |                  |                   |                         |                      |                |               |                        |               |               |
|                                                                                                                                          | •            | •                 |                         |              |                  | 1.5-13.0          | SDS plus                | 1                    | P1h            | 1             | 1                      | 3165140370073 | 2 608 572 227 |