

Digital HD Door Viewer

Art. no. TVAC80000B

Page 1 of 2



- Electronic spy hole for convenient front door surveillance
- Easy retrofitting within minutes
- Wireless installation, since it runs on batteries
- 2.4" color display with zoom effect
- HD 720p resolution: 1280 x 720 (individual images)
- Save three images to the microSD card upon activation to secure evidence

With this battery-operated, digital spy hole, you always see who is standing at your door.

Protection of your privacy

The video spy hole makes it easy for you and your family to recognize strangers at your door – thanks to HD resolution (720p) and the display with zoom function.

Very convenient

You'll never again have to "glue" your eye to the peephole while holding your other eye shut in order to see something. The digital spy hole offers a real alternative, since you can view the display with both eyes at a convenient distance.

Easy to operate

The monitor is activated with the push of a button, allowing you to see who is at your door: with both eyes and at a convenient distance from the door. The recording takes place automatically (three individual images) – in case you later want to know who it was.

More security for those home alone

The digital spy hole offers additional security for children and seniors in particular: that's because the image on the monitor is easy to make out even if you are not very tall and have to look at it from below!

Scope of delivery and installation

The scope of delivery includes everything that you need to retrofit the door – including an optical spy hole (14 mm), batteries, and a mount. Time needed for practiced hands: Just a few minutes!

Digital HD Door Viewer

Art. no. TVAC80000B

Page 2 of 2

Technical Data:

Battery operating time	Approx. 1300 activations
Resolution modes	1280 x 720 pixel
Battery type	2 x AA batteries
Image sensor	1/4" Progressive Scan CMOS-Sensor
Angle of view	180 °
Width	25 mm
Height	105 mm

Horizontal angle of view	60 °
Length	105 mm
Monitor	2,4" TFT LCD
Net weight	0,12 kg
Storage medium	Micro-SD-Card, max. 32 GB
Certifications	CE