

Drywall Cutter LXT®

DCO181

18V • 32 000 min⁻¹

Quick and handy drywall cutter

A light brushless cutter for cutting holes and shapes in drywall. Equipped with Auto-start Wireless System (AWS) function that makes it possible to connect tool to compatible vacuum cleaners with Bluetooth.



LXT **BL** **AWS**
MOTOR

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	32000 min ⁻¹
Collet Capacity	3,18 - 6,35 mm
Sound Pressure Level (L _{pA})	81 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Tool weight with battery	1,4 - 1,7 kg
Product Dimensions (L x W x H):	311 x 79 x 117 mm
AWS ready	✓
Sound Power Level (L _{WA})	89 dB(A)
Product net weight	1,0 kg
Vibration Level, Rotation Without Load	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor), Rotation Without Load	1,5 m/s ²
Vacuum cleaner connection Ø in / out	17 / 22 mm

User benefits

- Brushless maintenance-free and long-life motor
- LED light illuminates the work site
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Slide switch with lock-on for continuous use
- Electric brake for maximum productivity and increased operator safety
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing