



Cut



Medium Duty

High-visibility protective arm sleeves, ensuring user safety while offering superb comfort

- **Elevated comfort:** HyFlex® 11-202 arm protection sleeves are designed to provide a comfortable fit, offering plentiful space in the arm area, thereby reducing sweating and itchiness
- **Augmented dexterity:** The anatomical design of these protective arm sleeves is paired with a VELCRO® strap system, for an optimized fit and freedom of movement, for trouble-free productivity
- **Assured safety:** Their high-visibility exterior enhances safety and prevents workplace injuries
- **Heightened protection:** These protective sleeves also offer EN 407 level 1 thermal protection, safeguarding against heat up to 100°C/212°F, and meet ANSI/ISEA 105-2024 CUT A3 and EN ISO C protection standards to guard against lacerations



Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication

Applications

- Handling structural and body components
- Inspection, selecting, checking parts
- Body panel repair and replacement
- Glass repair and replacement
- Seizing structural and body parts
- Inspection (picking, checking and marking)
- Touching up
- Press shop operations
- Metalwork, glass processing

Key Features

- **Generous arm space:** Itchiness and sweating reduced, for added comfort
- **Anatomical design:** Extra freedom of movement, heightened productivity
- **High-visibility color:** More noticeable, for improved workplace safety

Performance Standards & Regulatory Compliance

ANSI/ISEA 105-2024



EN388: 2016



1X42C

EN 407



X1XXXX



Specifications

BRAND STYLE	DESCRIPTION	Gauge	LENGTH	PACKAGE
HyFlex® 11-202	Liner Material: Nylon, Polyester, Fiber glass Cuff Style: Knitwrist without thumbslot	13	19" - 475 mm	12 pieces/bag, 6 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 900
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Australia

Ansell Limited
Level 3, 678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699