


## PRODUCT PROFILE

### *edding 2200 C permanent marker*



#### **Product text**

- Permanent marker for marking and labelling almost all materials, e.g. paper, cardboard, metal, plastic and glass
- The chisel nib has a stroke width of 1-5 mm
- Waterproof and wear-resistant on almost all surfaces
- Available in 10 different colours
- The product is refillable
- Spare nibs are available
- Low-odour ink with no added toluene/xylene
- High-quality aluminium barrel

#### **Target group**

- Professionals e.g. in industry, craft, or public health who need markers with outstanding attributes for different materials, surfaces and applications
- Users who need to deliver a professional result
- Users with permanent marking needs in offices or administration rooms
- Users with organisational and structuring tasks around an office desk
- Households with 2+ persons
- Households with organizing, labelling and general marking needs

#### **Benefits for the consumer**

- Ready to use
- Cap can be stored on the end of the barrel to prevent risk of losing it
- Broad colour assortment
- High-quality brand product
- Made in Germany

#### **Product Information**

##### **Product ingredients**

- |                    |                      |
|--------------------|----------------------|
| Alcohol based ink  | • Yes                |
| Solvent based ink  | • Yes                |
| Dye based ink      | • Yes                |
| Excluded additives | • toluene and xylene |

##### **Product features**

- |                      |                    |
|----------------------|--------------------|
| Shape of nib         | • chisel           |
| Stroke width         | • 1-5 mm           |
| Spare nibs available | • Yes              |
| Permanent            | • Yes              |
| Low-odour            | • Yes              |
| Waterproof           | • Yes              |
| Wear-resistant       | • Yes              |
| Smudge-proof         | • Yes              |
| Lightfast            | • Yes              |
| Quick-drying         | • Yes              |
| Applicable on        | • Paper            |
|                      | • Carton/Cardboard |
|                      | • Rubber           |
|                      | • Plastic          |
|                      | • Glass            |
|                      | • Wood             |

Refillable  
Refillable with

Cap can be repositioned  
Roll stop present

**Product material**

Product material of cap  
Product material of mouthpiece  
Product material of barrel  
Product material of nib  
Product material of filter

**Dimensions & Logistics**

Width net  
Height net  
Depth net

**Colour**

Number of colours (product)  
Colour range of product (colour codes)  
Colour range of product (colour names)

Communication of writing colour by cap  
Communication of writing colour by barrel  
Communication of writing colour by mouthpiece

- Metal/Steel/Iron
- Concrete/Stone
- Ceramic
- Terracotta
- Leather
- Polystyrene
- Foils
- Yes
- edding T 25 refill ink
- edding MTK 25 refill ink in colour 001-004
- edding T 100 refill ink in colour 001-004
- Yes
- Yes

- PP
- PP
- Aluminium
- Acrylic
- Polyester

- mm
- mm
- mm

- 10
- 001-010
- black
- red
- blue
- green
- yellow
- orange
- brown
- violet
- pink
- light blue
- Yes
- Yes
- Yes

	SAP no.	KEA / order no.
Single product	526XXX	-
Folding box of 10 assorted (001-010)	1102999	4-2200C999
Blister of 1	8283XXX	4-2200C-1-1XXX

EAN code				
	Single product	Folding box	Outer carton	Shipping carton
002 red	4004764878529	4004764878536	-	4004764878543
001 black	4004764878499	4004764878505	-	4004764878512
002 red	4004764878529	4004764878536	-	4004764878543
003 blue	4004764878550	4004764878567	-	4004764878574
004 green	4004764878581	4004764878598	-	4004764878604
005 yellow	4004764950669	4004764950676	-	4004764950683
006 orange	4004764950690	4004764950706	-	4004764950713
007 brown	4004764950720	4004764950737	-	4004764950744
008 violet	4004764950751	4004764950768	-	4004764950775
009 pink	4004764950782	4004764950799	-	4004764950805
010 light blue	4004764950812	4004764950829	-	4004764950836
Folding box of 10 assorted (001-010)	4004764950843	-	-	4004764950850

<b>EAN code</b>				
	Single product	Folding box	Outer carton	Shipping carton
Folding box of 10 assorted (001-010)	4004764950843	-	-	4004764950850
Blister of 1 001 black	4004764893423	-	4004764893430	4004764893447
Blister of 1 002 red	4004764893867	-	4004764893874	4004764893881
Blister of 1 003 blue	4004764893898	-	4004764893904	4004764893911

<b>Packaging</b>					
	Net weight	Folding box	Outer carton	Shipping carton	Pallet
Single product	14,8 g	10 pcs	-	600 pcs	19.200 pcs
Folding box of 10 assorted (001-010)	14,8 g	-	-	60 pcs	1.920 pcs
Blister of 1	14,2 g	-	10 pcs	100 pcs	3.200 pcs