

Holesaws Bi-Metal – Cobalt



suttontools

32mm Cutting Depth

Industrial quality holesaw designed for machine or hand drilling in steel, stainless steel, cast iron, non-ferrous metals, plastic and wood.

Packed in a newly developed, space saving hang pack, featuring clear dimensional markings making selection easy. Visually appealing form makes any retail shelves come to life.

Varied Pitched Teeth
Reduces vibration for cleaner finish and greater accuracy



Fast ejection slots

International Thread Standard
Accepts all arbors

Made from Bi-Metal Cobalt HSS
For toughness and longer life

Application

- DIY
- Trade
- Automotive
- Electrical
- Plumbing
- Carpentry
- General Contracting
- Woodworking
- Metalworking
- Machine Shop
- MRO



H125 S1



H125 S3



H125 S5



H125 S11



H125 S7



H125 S9



H125 S14

Description	Arbor	Pilot	Pieces	Item #	Barcode
Heavy Duty Bi-Metal Holesaw Sets					H125
Starter Set Holesaws: 20, 25, 32, 38 & 54mm	UA2 & BA	BD24	5	H125 S1	9311963625409
Carpenter Set Holesaws: 32, 38, 51, 54, 76, 92 & 105mm	UA3	BD24	7	H125 S3	9311963625416
General Purpose Set Holesaws: 16, 19, 22, 25, 29, 32, 35, 38, 44 & 51mm	UA1, UA3 & BA	2x BD24	10	H125 S5	9311963625423
Plumber Set Holesaws: 41, 51, 57, 73, 86 & 111mm	UA3	BD24	6	H125 S7	9311963625430
Electrician Set Holesaws: 16, 20, 25, 32, 40 & 51mm	UA1 & UA3	2x BD24	6	H125 S9	9311963625447
Lock Installation Kit Holesaws: 22, 25 & 54mm	BA1 & adaptor 1 x door lock guide		3	H125 S11	9311963625454
Maintenance Set Holesaws: 19, 22, 25, 32, 35, 38, 44, 51, 57, 63 & 76mm	UA1, UA3 & BA	2x BD24	11	H125 S14	9311963625461