



tesa® 64250

Product Information



Flexible transport securing tape

Product Description

tesa® 64250 combines flexibility with the strength of a tensilised polypropylene backing.

Product Features

- Due to its outstanding conformability the product is ideally suited for applications on “3-dimensional” surfaces.
- tesa® 64250 can be removed residue- and discoloration-free from a variety of different surfaces.

Application Fields

Transport securing of office automation equipment such as printers, scanners, copying machines as well as appliances.

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|---------|-------------------|-------|
| • Backing | MOPP | • Total thickness | 79 µm |
| • Type of adhesive | acrylic | | |

Properties/Performance Values

- | | | | |
|-----------------------|----------|-----------------------------|-----|
| • Elongation at break | 30 % | • No discoloration | yes |
| • Tensile strength | 100 N/cm | • Residue-free removability | yes |

Adhesion to Values

- | | |
|---------|--------|
| • Steel | 3 N/cm |
|---------|--------|

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?ip=64250>