
ΩDBK HPG 1/10 60X35 12-24V


Contact type PTC heating element

Prepared: 16/9/2026

Specification Table	
Marking	ΩDBK HPG 1/10 60X35 12-24V Date Code
Sample reference	VS10377_SR2327-2
DBK Article Number	1001128
ETL Number (ETL Article Number)	7256455 (1001130)
Voltage (V)	12-24 VAC
Surface Temp (Ts)	100°C +5/-10°C at 24V, still air & 25°C±2°C
Inrush currnet, Ir	≤7A at 24V, still air & 25°C±2°C
Leadwire	Silicone UL3135 AWG 20 (white) L = 100mm ±5.0 Splice Crimp 6mm



Leadwire length
not shown to scale



E481/201903

DBK Technology Ltd. © Information subject to change without notice.

Tel: +44 (0) 1162 796899
info@etdyn.com
www.etdyn.com