

Main

Range of product	TeSys U
Device short name	LUF
Product or component type	Communication gateway
Product compatibility	ATS48 ATV31 TeSys U starter-controllers

Complementary

Type of connector	RJ45 Modbus RJ45 to a PC Female SUB-D 9 field bus
Maximum number of connections	<= 8 Modbus slaves
[Us] rated supply voltage	24 V DC +/- 10 %
Current consumption	100 mA typical 280 mA maximum
Local signalling	LED front panel
Services	Command - bus type: Profibus DP - functions available: 122 configurable words Configuration and adjustment - bus type: Fipio - functions available: by gateway mini messaging facility Monitoring - bus type: Profibus DP - functions available: 122 configurable words
Product weight	0.245 kg

Environment

Electromagnetic compatibility	Electromagnetic emission conforming to IEC 50081-2 Electromagnetic immunity conforming to IEC 61000-6-2
Pollution degree	2 conforming to IEC 60664
Ambient air temperature for installation	5...50 °C
IP degree of protection	IP20
RoHS EUR conformity date	0852
RoHS EUR status	Compliant